



# Maxos, montážne zariadenie

## 9MX056 MB-SW L3000 BK

ACC MAXOS, Čierna

The light line fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

### Údaje o produkte

Všeobecné informácie		Úplný názov produktu	9MX056 MB-SW L3000 BK
Farba príslušenstva	Čierna	Úplný kód produktu	403073225988500
Kód radu produktov	9MX056 [ACC MAXOS]	Objednávkový kód	25988500
Schválenie a použitie		Č. materiálu (12NC)	910605149426
Krytie IP	-	Čitateľ – množstvo kusov v balení	1
Trieda ochrany IEC	-	EAN/UPC – produkt/puzdro	4030732259885
Údaje o produkte		Čitateľ – počet balení v krabici	1
Objednávkový názov produktu	9MX056 MB-SW L3000 BK	EAN/UPC – balenie	4030732259885