



Maxos mounting accessories

9MX056 MB-SW WH

ACC MAXOS, White

The light line fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

Product data

| General Information | |
|--------------------------|--------------------|
| Accessory colour | White |
| Product family code | 9MX056 [ACC MAXOS] |
| Approval and Application | |
| Ingress protection code | - |
| Protection class IEC | - |
| Product Data | |
| Order product name | 9MX056 MB-SW WH |

| | |
|-----------------------------------|-----------------|
| Full product name | 9MX056 MB-SW WH |
| Full EOC | 403073266280799 |
| Order code | 66280799 |
| Material no. (12 NC) | 910605149626 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 4030732662807 |
| Numerator – packs per outer box | 10 |
| EAN/UPC - Case | 4030732259908 |