



Maxos, TL-D IP64 trunking

4MX056 583 5x1.5 IP64 WH

MAXOS TST8, Dust penetration-protected, splashproof, White

The IP 64 trunking sections are made of hot-dip galvanised steel, and are coated white. They are available in lengths of 1, 2 and 3 electrical units 36 W and 58 W. Special sealings between the sections and waterproof trunking end pieces are used (accessories). A flat ribbon cable (5 or 7 wires) is integrated in the trunking and guarantees (in combination with an integrated phase selection switch and contact blocks) a safe and correct cabling. The 7-wire cable is used to integrate light regulation or emergency lighting for those electrical units equipped with emergency battery packs. Hence, no extra contact blocks or wiring needs to be installed. For suspended light-lines the trunking sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface mounted lightlines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the trunking section special knockout openings enable cable entry wherever needed. The IP 64 trunking can be equipped with special IP 64 electrical units plus different reflectors or with completely closed reflector units that include a glass cover (IP 54). The outstanding stability of the sections and coupling pieces allows suspension intervals between 3.4 m up to 5 m (see chart).

Product data

General Information	
Product family code	4MX056 [MAXOS TST8]
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark


Mechanical and Housing	
Housing Color	White
Overall length	4,590 mm

Maxos, TL-D IP64 trunking

Approval and Application	
Ingress protection code	IP64 [Dust penetration-protected, splashproof]
Protection class IEC	Safety class I
Product Data	
Order product name	4MX056 583 5x1.5 IP64 WH
Full product name	4MX056 583 5x1.5 IP64 WH
Full product code	403073257844399

Order code	57844399
Material Nr. (12NC)	910610016626
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732578443
Numerator - Packs per outer box	2
EAN/UPC - Case	4030732104673

Dimensional drawing



Product
4MX056 583 5x1.5 IP64 WH

