



Maxos, TL-D extended trunking

4MX056 582 M600/E600 5x1.5 WH

MAXOS TST8, White

The extended trunking sections are made of hot-dip galvanised steel, with a white or silver coating. They are available in lengths of 1 and 2 electrical units of 58 W. Extensions of 300, 600, 850, 950 and 1110 mm in the middle only, or in the middle and at the end of these trunking sections allow interrupted lines. That means gaps between the electrical units corresponding to the extensions. The gaps can be filled by blind covers, available as accessories. A flat ribbon cable (5 wires) is integrated in the trunking and guarantees (in combination with an integrated phase selection switch and contact blocks) a safe and correct cabling. For suspended light-lines the trunking sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface mounted lightlines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the trunking section special knockout openings enable cable entry wherever needed.

Product data

General Information	
Product family code	4MX056 [MAXOS TST8]
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Mechanical and Housing	
Housing Color	White
Overall length	3,060 mm


Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Product Data	
Order product name	4MX056 582 M600/E600 5x1.5 WH
Full product name	4MX056 582 M600/E600 5x1.5 WH
Full product code	403073255395299
Order code	55395299

Maxos, TL-D extended trunking

Material Nr. (12NC)	910610018126
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732553952
Numerator - Packs per outer box	2

EAN/UPC - Case	4030732104772
----------------	---------------

Dimensional drawing



Product
4MX056 582 M600/E600 5x1.5 WH

