



# Maxos, TL-D standard trunking

4MX056 361 2x5x2.5 SI

MAXOS TST8, Silver

The trunking fulfils two functions: first it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. All the trunking sections are made of hot-dip galvanised steel, with a white or silver coating. They are available in lengths of 1, 2 and 3 electrical units 36 W and 58 W. A flat ribbon cable (5 or 7 wires) or two flat ribbon cables (2x5 or 2x7 wires) are integrated in the trunking and guarantee (in combination with an integrated phase selection switch and contact blocks) a safe and correct cabling. The 7-wire cable is used to integrate light regulation or emergency lighting for those electrical units equipped with emergency battery packs. Double wiring (2x5 or 2x7 wires) is needed to provide a completely separate mains supply to the electrical units. Double wiring is mostly used for emergency lighting by central emergency batteries or separate switching. Hence, no extra contact blocks or wiring needs to be installed.

## Product data

General Information	
Product family code	4MX056 [MAXOS TST8]
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Mechanical and Housing	
Housing Color	Silver
Overall length	1,230 mm


Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Product Data	
Order product name	4MX056 361 2x5x2.5 SI
Full product name	4MX056 361 2x5x2.5 SI
Full product code	403073253689499
Order code	53689499

Maxos, TL-D standard trunking

Material Nr. (12NC)	910616024126
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732536894
Numerator - Packs per outer box	2

EAN/UPC - Case	4030732106028
----------------	---------------

Dimensional drawing



Product
4MX056 361 2x5x2.5 SI

