



Koffer² SGP070

SGP070 2xSON-T70W II RW FG AL9007 DB

2, SON-T, 70 W, Safety class II, Reflector for railways, Flat glass, Gray aluminum (RAL9007)

Koffer² is an archetypal modern road lighting luminaire which meets the needs of today's road users and operators. Total cost over lifetime was a key consideration in the development of Koffer². The future-proof luminaire delivers outstanding optical performance, enabling optimum spacing and energy efficiency, and is easy to install and maintain. With its rectangular shape, Koffer² offers an alternative to rounded luminaires. It is available in three sizes – for mounting heights from 3.5 to 12 meters – and with dedicated masts and brackets, making it equally suitable for integration into modern urban environments or more traditional lighting designs. The Koffer² family accommodates CosmoPolis white-light technology and LED-enabled versions. Each Koffer² luminaire is fully recyclable; only the light source and driver have to be recycled separately.

Product data


General Information		Optic type outdoor	
Lamp family code	SON-T [SON-T]	Reflector for railways	
Gear	CONV [Conventional]	Operating and Electrical	
Photocell	-	Input Voltage	230 V
Embedded control	-	Power Consumption	70 W
CE mark	Yes	Cable	-
ENEC mark	ENEC mark	Mechanical and Housing	
Light Technical		Parts color	All parts colored
Standard tilt angle posttop	10°	Approval and Application	
Number of light sources	2	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Optical cover type	Flat glass		

Koffer² SGP070

Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II
Product Data	
Order product name	SGP070 2xSON-T70W II RW FG AL9007 DB
Full product name	SGP070 2xSON-T70W II RW FG AL9007 DB
Full product code	403073223996200
Order code	910616611121

Material Nr. (12NC)	910616611121
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732239962
Numerator - Packs per outer box	1
EAN/UPC - Case	4030732239962

Dimensional drawing



Product	A
SGP070 2xSON-T70W II RW FG AL9007 DB	133 mm

