



Maxos LED Performer

4MX900 491 LED40S/840 PSU A30 WH

Maxos LED Performer, Generation 3, LED module, system flux 4000 lm, 840 neutral white, Power supply unit (On/Off), Asymmetrical mirror axis angle 30°, White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Product data

| General Information | | | |
|--------------------------|--|----------------------------------|-----------------------------------|
| Lamp family code | LED40S [LED module, system flux 4000 lm] | CE mark | Yes |
| Light source replaceable | No | Warranty period | 5 years |
| Number of gear units | Unit | Flammability mark | - |
| Driver included | Yes | ENEC mark | ENEC mark |
| Remarks | *- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. | Glow-wire test | Temperature 650 °C, duration 30 s |
| | | EU RoHS compliant | Yes |
| Product family code | 4MX900 [Maxos LED Performer] | Light Technical | |
| Lighting Technology | LED | Luminous Flux | 4,000 lm |
| Value ladder | Performance | Saturated Red (R9) | <50 |
| | | Correlated Colour Temperature | 4000 K |
| | | Luminous efficacy (rated) (nom.) | 159 lm/W |
| | | Colour rendering index (CRI) | ≥80 |
| | | Number of light sources | 1 |
| | | Beam angle of light source | 120 degree(s) |
| | | Light source colour | 840 neutral white |

Maxos LED Performer

| | |
|-----------------------------|------------------------------------|
| Optic type | Asymmetrical mirror axis angle 30° |
| Luminaire light beam spread | 30° |
| Unified Glare Rating (CEN) | Not applicable |

Operating and Electrical

| | |
|--|------------------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 17.8 A |
| Inrush time | 0.282 ms |
| Power Consumption | 25.2 W |
| Power Factor (Fraction) | 0.9 |
| Connection | Connection unit 3-pole |
| Cable | - |
| Number of products on MCB of 16 A type B | 24 |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +40 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|----------------------------|
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface | - |
| Constant light output | No |

Mechanical and Housing

| | |
|-------------------------------------|-------------------------|
| Housing material | Aluminium |
| Reflector material | - |
| Optic material | Polymethyl methacrylate |
| Optical cover/lens material | Polymethyl methacrylate |
| Fixation material | Steel |
| Housing Colour | White |
| Optical cover/lens finish | Clear |
| Overall length | 1,479 mm |
| Overall width | 87 mm |
| Overall height | 82 mm |
| Dimensions (height x width x depth) | 82 x 87 x 1479 mm |

Approval and Application

| | |
|-------------------------|-----------------------|
| Ingress protection code | IP40 [Wire-protected] |
|-------------------------|-----------------------|

| | |
|------------------------------|--|
| Mech. impact protection code | IK02 [0.2 J standard] |
| Sustainability rating | - |
| Protection class IEC | Safety class I |
| Photobiological risk | Photobiological risk group 0 @200mm to EN62778 |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|------------------------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.38, 0.38) SDCM <3.5 |
| Power consumption tolerance | +/-10% |

Over Time Performance (IEC Compliant)

| | |
|---|------|
| Control gear failure rate at median useful life 50,000 h | 5 % |
| Control gear failure rate at median useful life 100,000 h | 10 % |
| Lumen maintenance at median useful life* 50,000 h | L90 |
| Lumen maintenance at median useful life* 100,000 h | L80 |

Application Conditions

| | |
|------------------------------------|----------------|
| Performance ambient temperature Tq | 25 °C |
| Maximum dim level | Not applicable |
| Suitable for random switching | Not applicable |

Product Data

| | |
|-----------------------------------|----------------------------------|
| Order product name | 4MX900 491 LED40S/840 PSU A30 WH |
| Full product name | 4MX900 491 LED40S/840 PSU A30 WH |
| Full EOC | 403073266638699 |
| Order code | 66638699 |
| Material no. (12 NC) | 910629145826 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 4030732666386 |
| Numerator – packs per outer box | 2 |
| EAN/UPC – Case | 4030732264551 |

Maxos LED Performer

Dimensional drawing

