



Maxos LED inserts for TTX400

4MX400 491 LED55S/840 PSU WB WH

Maxos LED Retrofit for TTX400, LED Module, system flux 5500 lm, 840 neutral white, Power supply unit (On/Off), Wide beam, White

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED inserts for TTX400 a truly future-proof solution.

Product data

| General Information | |
|--------------------------|--|
| Lamp family code | LED55S [LED Module, system flux 5500 lm] |
| Cap-Base | - [-] |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Gear | - |
| Driver included | Yes |
| Remarks | *-Per Lighting Europe guidance paper *Evaluating performance of LED based |

| | |
|--|--|
| luminaires - January 2018*: statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. | |
| Product family code | 4MX400 [Maxos LED Retrofit for TTX400] |
| Lighting Technology | LED |
| Value ladder | Performance |
| CE mark | Yes |

Maxos LED inserts for TTX400

| | |
|-------------------|-----------------------------------|
| Warranty period | 5 years |
| Flammability mark | - |
| ENEC mark | ENEC mark |
| Glow-wire test | Temperature 650 °C, duration 30 s |
| EU RoHS compliant | Yes |

Light Technical

| | |
|------------------------------------|------------------------------------|
| Luminous Flux | 5,500 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 167 lm/W |
| Color rendering index (CRI) | ≥80 |
| Number of light sources | 1 |
| Beam angle of light source | 120 degree(s) |
| Light source color | 840 neutral white |
| Optic type | Wide beam |
| Optical cover type | Polymethyl methacrylate bowl/cover |
| Luminaire light beam spread | 90° |
| Unified glare rating CEN | Not applicable |

Operating and Electrical

| | |
|--|------------------------|
| Input Voltage | 220-240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 17.8 A |
| Inrush time | 0.282 ms |
| Power Consumption | 33 W |
| Power Factor (Fraction) | 0.9 |
| Connection | Connection unit 3-pole |
| Cable | - |
| Number of products on MCB of 16 A type B | 24 |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +35 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|----------------------------|
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Constant light output | No |

Mechanical and Housing

| | |
|--------------------|-------|
| Housing Material | Steel |
| Reflector material | - |

| | |
|-------------------------------------|-------------------------|
| Optic material | Polymethyl methacrylate |
| Optical cover material | Polymethyl methacrylate |
| Fixation material | Steel |
| Housing Color | White |
| Optical cover finish | Clear |
| Overall length | 1,474 mm |
| Overall width | 63 mm |
| Overall height | 50 mm |
| Dimensions (Height x Width x Depth) | 50 x 63 x 1474 mm |

Approval and Application

| | |
|------------------------------|-------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Protection class IEC | Safety class I |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|------------------------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.38, 0.38) SDCM <3.5 |
| Power consumption tolerance | +/-10% |

Over Time Performance (IEC Compliant)

| | |
|---|-----|
| Control gear failure rate at median useful life 50000 h | 5 % |
| Lumen maintenance at median useful life* 50000 h | L80 |

Application Conditions

| | |
|------------------------------------|----------------|
| Performance ambient temperature Tq | 25 °C |
| Suitable for random switching | Not applicable |

Product Data

| | |
|---------------------------------|---------------------------------|
| Order product name | 4MX400 491 LED55S/840 PSU WB WH |
| Full product name | 4MX400 491 LED55S/840 PSU WB WH |
| Full product code | 403073266583999 |
| Order code | 910629156226 |
| Material Nr. (12NC) | 910629156226 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 4030732665839 |
| Numerator - Packs per outer box | 3 |
| EAN/UPC - Case | 4030732263981 |

Maxos LED inserts for TTX400

Dimensional drawing

