



Maxos LED inserts for TTX400

4MX400 491 LED66S/840 PSD NB WH

Maxos LED Retrofit for TTX400, Generation 4, LED module, system flux 6600 lm, 840 neutral white, Power supply unit with DALI interface, Narrow beam, Connection unit 5-pole, White

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required colour temperatures and glare factors. The minimalistic Maxos LED Industry 4MX400 panel inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED Industry 4MX400 panel inserts for TTX400 a truly future-proof solution.

Product data

General Information		
Lamp family code	LED66S [LED module, system flux 6600 lm]	LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	
Number of gear units	Unit	
Gear	-	
Driver included	Yes	
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of	
Product family code	4MX400 [Maxos LED Retrofit for TTX400]	
Lighting Technology	LED	

Maxos LED inserts for TTX400

Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	6.600 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	169 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Narrow beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	50°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.28 ms
Power Consumption	39 W
Power Factor (Fraction)	0.97
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate

Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	1,474 mm
Overall width	63 mm
Overall height	50 mm
Dimensions (height x width x depth)	50 x 63 x 1474 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

Product Data

Order product name	4MX400 491 LED66S/840 PSD NB WH
Full product name	4MX400 491 LED66S/840 PSD NB WH
Full EOC	403073266833599
Order code	66833599
Material no. (12 NC)	910629162726
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732668335
Numerator – packs per outer box	3
EAN/UPC – Case	4030732267095

Maxos LED inserts for TTX400

Dimensional drawing

