



Maxos TL5 standard trunking

4MX656 493 2x7x2.5 WH

MAXOS TST5, Λευκό

The trunking fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. All the light-line sections are made of hot-dip galvanized steel with a white or silver finish. They are available in dedicated TL5 lengths of 1, 2 and 3 electrical units 49 W (35/80 W) and 54 W (28 W). A flat ribbon cable (5 or 7 wires) or two flat ribbon cables (2 x 5 or 2 x 7 wires) are integrated in the trunking and guarantee (in combination with an integrated phase selection switch and contact blocks) safe and correct cabling. The 7-wire cable is used to integrate light regulation or emergency lighting for those electrical units that are equipped with emergency battery packs. Double wiring (2 x 5 or 2 x 7 wires) is needed to provide a completely separate mains supply to the electrical units. Double wiring is mostly used for emergency lighting by central emergency batteries or separate switching. Hence, no extra contact blocks or wiring are required. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The trunking is available with a complete range of interchangeable components that optimize flexibility. The outstanding stability of the sections and coupling pieces allows suspension intervals of 3.4 to 5 m. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

Δεδομένα Προϊόντων

Maxos TL5 standard trunking

Γενικές πληροφορίες

Κωδικός ονομασίας σειράς	4MX656 [MAXOS TST5]
Σήμανση ευφλεκτότητας	Για τοποθέτηση σε εύφλεκτες επιφάνειες
Σήμανση ENEC	Σήμανση ENEC

Μηχανικά εξαρτήματα και Περιβλήμα

Χρώμα περιβλήματος	Λευκό
Συνολικό μήκος	4.437 mm

Έγκριση και Εφαρμογή

Βαθμός προστασίας από τις εισροές	IP20 [Με προστασία για δάχτυλα]
Κατηγορία προστασίας IEC	Κατηγορία ασφαλείας I

Στοιχεία προϊόντος

Όνομα παραγγέλιας προϊόντος	4MX656 493 2x7x2.5 WH
-----------------------------	-----------------------

Πλήρες όνομα προϊόντος	4MX656 493 2x7x2.5 WH
Full EOC	403073258378299
Υπολογισμένη περιγραφή τοπικού κωδικού B2B	4MX656/493WH14
Κωδικός παραγγελίας	58378299
Αρ. υλικού (12NC)	910631157326
Τοπικός κωδικός	4MX656/493WH14
Αριθμητής - Ποσότητα ανά συσκευασία	1
EAN/UPC - Προϊόν/Θήκη	4030732583782
Αριθμητής SAP - Πακέτα ανά εξωτερικό κουτί	2
EAN/UPC - Κιβώτιο	4030732198535

Σχεδιάγραμμα διαστάσεων

