



# Maxos, swivel device

## 9MX056 MB-ST-L1250 SI

ACC MAXOS, Silver

The swivel device enables variable angles between the lines, and it is suitable for MAXOS TL-D and TL5. The minimum angle is 45 degrees. Due to its modern design it is often used in application areas such as shops, schools and museums. Up to four trunking sections can be connected with one swivel device. The housing is made of plastic, with a white or silver coating, and with inner supporting elements made of steel. If needed the swivel device can accommodate light sensors, cameras, spotlight adapters, loud speakers, etc., by dividing it into two chambers. It is pre-mounted with an infinitely adjustable quick hanger with a 1.25 m steel suspension wire. One coupling piece per trunking section is necessary to connect the trunking to the swivel device.

### Product data

<b>General Information</b>		<b>Full product name</b>	9MX056 MB-ST-L1250 SI
Accessory color	Silver	Full product code	403073264028799
Product family code	9MX056 [ACC MAXOS]	Order code	64028799
<b>Approval and Application</b>		Material Nr. (12NC)	910680016626
Ingress protection code	-	Numerator - Quantity Per Pack	1
Protection class IEC	-	EAN/UPC - Product/Case	4030732640287
<b>Product Data</b>		Numerator - Packs per outer box	10
Order product name	9MX056 MB-ST-L1250 SI	EAN/UPC - Case	4030732107919