



Maxos, swivel device

9MX056 MB-ST-L1250 SI

ACC MAXOS, Silver

The swivel device enables variable angles between the lines, and it is suitable for MAXOS TL-D and TL5. The minimum angle is 45 degrees. Due to its modern design it is often used in application areas such as shops, schools and museums. Up to four trunking sections can be connected with one swivel device. The housing is made of plastic, with a white or silver coating, and with inner supporting elements made of steel. If needed the swivel device can accommodate light sensors, cameras, spotlight adapters, loud speakers, etc., by dividing it into two chambers. It is pre-mounted with an infinitely adjustable quick hanger with a 1.25 m steel suspension wire. One coupling piece per trunking section is necessary to connect the trunking to the swivel device.

Product data

General Information	
Accessory color	Silver
Product family code	9MX056 [ACC MAXOS]
Approval and Application	
Ingress protection code	-
Protection class IEC	-
Product Data	
Order product name	9MX056 MB-ST-L1250 SI

Full product name	9MX056 MB-ST-L1250 SI
Full product code	403073264028799
Order code	910680016626
Material Nr. (12NC)	910680016626
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732640287
Numerator - Packs per outer box	10
EAN/UPC - Case	4030732107919