



# Maxos, mounting accessories

## 9MX056 CF-SW-L1250 ZC

ACC MAXOS, Steel

The light line fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

### Product data

|                                 |                       |                                 |                       |
|---------------------------------|-----------------------|---------------------------------|-----------------------|
| <b>General Information</b>      |                       | <b>Full product name</b>        | 9MX056 CF-SW-L1250 ZC |
| Accessory color                 | Steel                 | Full product code               | 403073256709600       |
| Product family code             | 9MX056 [ACC MAXOS]    | Order code                      | 910680029326          |
| <b>Approval and Application</b> |                       | Material Nr. (12NC)             | 910680029326          |
| Ingress protection code         | -                     | Numerator - Quantity Per Pack   | 1                     |
| Protection class IEC            | -                     | EAN/UPC - Product/Case          | 4030732567096         |
| <b>Product Data</b>             |                       | Numerator - Packs per outer box | 1                     |
| Order product name              | 9MX056 CF-SW-L1250 ZC | EAN/UPC - Case                  | 4030732567096         |