



Maxos, montážne zariadenie

9MX056 CF-SW-L1250 ZC

ACC MAXOS, Oceľ

The light line fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

Údaje o produkte

Všeobecné informácie		Úplný názov produktu	
Farba príslušenstva	Oceľ	Úplný kód produktu	9MX056 CF-SW-L1250 ZC
Kód radu produktov	9MX056 [ACC MAXOS]	Objednávkový kód	403073256709600
Schválenie a použitie		Č. materiálu (12NC)	56709600
Krytie IP	-	Čitateľ – množstvo kusov v balení	910680029326
Trieda ochrany IEC	-	EAN/UPC – produkt/puzdro	1
Údaje o produkte		Čitateľ – počet balení v krabici	4030732567096
Objednávkový názov produktu	9MX056 CF-SW-L1250 ZC	EAN/UPC – balenie	1
			4030732567096