



Maxos, TL-D IP64 trunking

9MX056 BC58 IP64 WH

ACC MAXOS, Dust penetration-protected, splashproof, White

The IP64 trunking sections are made of hot-dip galvanized steel with a white powder coating. They are available in lengths of 1, 2 and 3 electrical units 36 and 58 W. Special seals between the sections and waterproof trunking end-pieces are used (please order separately). A flat ribbon cable (5 or 7 wires) is integrated in the trunking and guarantees (in combination with an integrated phase selection switch and contact blocks) safe and correct cabling. The 7-wire cable is used to integrate light regulation or emergency lighting for those electrical units that are equipped with emergency battery packs. Hence, no extra contact blocks or wiring need to be installed. For suspended light-lines, the trunking sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the trunking section, special knock-out openings enable cable entry wherever needed. The IP64 trunking can be equipped with special IP64 electrical units and different reflectors. The outstanding stability of the sections and coupling pieces allows suspension intervals of 3.4 to 4.8 m.

Product data

General Information		Protection class IEC	
Accessory color	White	-	
Product family code	9MX056 [ACC MAXOS]	Product Data	
Approval and Application		Order product name	9MX056 BC58 IP64 WH
Ingress protection code	IP64 [Dust penetration-protected, splashproof]	Full product name	9MX056 BC58 IP64 WH
		Full product code	403073253872099

Maxos, TL-D IP64 trunking

Order code	910683002926
Material Nr. (12NC)	910683002926
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732538720

Numerator - Packs per outer box	18
EAN/UPC - Case	4030732108282

