



# Maxos, TL-D extended trunking

## 9MX056 BC L600 WH

ACC MAXOS, White

The extended trunking sections are made of hot-dip galvanized steel with a white or silver finish. They are available in lengths of 1 and 2 electrical units of 58 W. Extensions of 300 and 600 mm in the middle only (M), or in the middle and at the end of these trunking sections (ME), allow interrupted lines where the gaps between the electrical units correspond to the extended trunking length. The gaps can be filled by blind covers, available as accessories. A flat ribbon cable (5 wires) is integrated in the trunking and guarantees (in combination with an integrated phase selection switch and contact blocks) safe and correct cabling. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the trunking section, special knock-out openings enable cable entry wherever needed.

### Product data

General Information	
Accessory color	White
Product family code	9MX056 [ACC MAXOS]
Approval and Application	
Ingress protection code	-
Protection class IEC	-

Product Data	
Order product name	9MX056 BC L600 WH
Full product name	9MX056 BC L600 WH
Full product code	403073253876899
Order code	910683007426
Material Nr. (12NC)	910683007426
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732538768
Numerator - Packs per outer box	4

Maxos, TL-D extended trunking

EAN/UPC - Case	4030732108404
----------------	---------------

