



Maxos, TL-D extended trunking

9MX056 BC-L300 SI

ACC MAXOS, Silver

The extended trunking sections are made of hot-dip galvanised steel, with a white or silver coating. They are available in lengths of 1 and 2 electrical units of 58 W. Extensions of 300, 600, 850, 950 and 1110 mm in the middle only, or in the middle and at the end of these trunking sections allow interrupted lines. That means gaps between the electrical units corresponding to the extensions. The gaps can be filled by blind covers, available as accessories. A flat ribbon cable (5 wires) is integrated in the trunking and guarantees (in combination with an integrated phase selection switch and contact blocks) a safe and correct cabling. For suspended light-lines the trunking sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface mounted lightlines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the trunking section special knockout openings enable cable entry wherever needed.

Product data

General Information	
Accessory color	Silver
Product family code	9MX056 [ACC MAXOS]
Approval and Application	
Ingress protection code	-
Protection class IEC	-

Product Data	
Order product name	9MX056 BC-L300 SI
Full product name	9MX056 BC-L300 SI
Full product code	403073253882999
Order code	53882999
Material Nr. (12NC)	910683008326
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732538829
Numerator - Packs per outer box	5

Maxos, TL-D extended trunking

EAN/UPC - Case

4030732108459

