



Maxos accessories

9MX056 2EP 2EC7 WH

ACC MAXOS, Biel

The swivel device is a versatile mechanical connecting device for Maxos TL-D and TL5 light-lines and enables variable angles between the light-lines. The minimum angle is 45 degrees. Due to its attractive design it is often used in application areas such as shops, schools and museums. Up to four light-lines can be connected with one swivel device. The housing is made of plastic, with a white or silver coating, and with inner supporting elements made of steel. If needed, the swivel device can accommodate lighting control sensors, loudspeakers, etc. It is pre-mounted with an adjustable quick hanger with a 1.25 m steel suspension wire. One dedicated coupling piece (9MX056 CP-SD WH/SI) per trunking section is necessary to connect the trunking to the swivel device. Electrical components for mains feed-through have to be ordered as required.

Dane produktu

Informacje ogólne	
Kolor akcesorium	Biel
Rodzina produktów	9MX056 [ACC MAXOS]
Eksploatacja i połączenie elektryczne	
Napięcie wejściowe	220 do 240 V
Częstotliwość linii	50 to 60 Hz
Certyfikaty i zastosowania	
Kod stopnia ochrony	-
Klasa ochrony IEC	Klasa bezpieczeństwa I

Dane techniczne produktu	
Nazwa produktu na zamówieniu	9MX056 2EP 2EC7 WH
Pełna nazwa produktu	9MX056 2EP 2EC7 WH
Full EOC	403073212359900
Kod zamówienia	12359900
Materiał Nr (12NC)	910683009026
Numerator - Quantity Per Pack	1
EAN/UPC - Produkt/opakowanie	4030732123599
Numerator - Packs per outer box	1
EAN/UPC - Opakowanie	4030732123599