



Maxos TL5, aluminum reflectors and optics

9MX056 EP/TL5 SI

ACC MAXOS, Silver

The aluminum reflectors for TL5 are optimised for applications in supermarkets, shops and industry. They are made of high-quality aluminum and are available for electrical units holding 1 or 2 TL5 lamps. A semi-high-gloss (D) aluminum reflector is available for wide-beam, medium-beam, narrow-beam, asymmetrical-beam and double-asymmetrical-beam light distributions. For very narrow beams a high-gloss (C) aluminum reflector is available. All the TL5 aluminum reflectors can be equipped with aluminum louvers with profiled lamellae (M2) or with a simple white steel louver (L) for glare reduction. The reflector is fixed to the electrical unit via a simple click. The reflectors can be connected to each other in a line by a material overlap; optional additional coupling pieces (9MX056 CP/TL5) are available. Decorative end plates for the beginning and end of the line are available as accessories.

Product data

General Information	
Accessory color	Silver
Product family code	9MX056 [ACC MAXOS]
Approval and Application	
Ingress protection code	-
Protection class IEC	-
Product Data	
Order product name	9MX056 EP/TL5 SI

Full product name	9MX056 EP/TL5 SI
Full product code	403073255283200
Order code	55283200
Material Nr. (12NC)	910684014221
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732552832
Numerator - Packs per outer box	1
EAN/UPC - Case	4030732552832