



Maxos TL5, aluminum reflectors and optics

9MX056 EP/TL5 SI

ACC MAXOS, Silver

The aluminum reflectors for TL5 are optimised for applications in supermarkets, shops and industry. They are made of high-quality aluminum and are available for electrical units holding 1 or 2 TL5 lamps. A semi-high-gloss (D) aluminum reflector is available for wide-beam, medium-beam, narrow-beam, asymmetrical-beam and double-asymmetrical-beam light distributions. For very narrow beams a high-gloss (C) aluminum reflector is available. All the TL5 aluminum reflectors can be equipped with aluminum louvers with profiled lamellae (M2) or with a simple white steel louver (L) for glare reduction. The reflector is fixed to the electrical unit via a simple click. The reflectors can be connected to each other in a line by a material overlap; optional additional coupling pieces (9MX056 CP/TL5) are available. Decorative end plates for the beginning and end of the line are available as accessories.

Product data

| | | | |
|---------------------------------|--------------------|---------------------------------|------------------|
| General Information | | Full product name | 9MX056 EP/TL5 SI |
| Accessory color | Silver | Full product code | 403073255283200 |
| Product family code | 9MX056 [ACC MAXOS] | Order code | 910684014221 |
| Approval and Application | | Material Nr. (12NC) | 910684014221 |
| Ingress protection code | - | Numerator - Quantity Per Pack | 1 |
| Protection class IEC | - | EAN/UPC - Product/Case | 4030732552832 |
| Product Data | | Numerator - Packs per outer box | 1 |
| Order product name | 9MX056 EP/TL5 SI | EAN/UPC - Case | 4030732552832 |