



# Maxos TL5, facet reflectors and optics

## 9MX056 EP-F WH

ACC MAXOS, White

Facetted reflectors for TL5 give shops and offices a high-class appearance. They are made of steel, with a white or silver finish, and are available for electrical units holding 1 or 2 TL5 lamps. The facetted reflector can be integrated with a semi-high-gloss (D6) OLC optic of high-quality aluminum and has parabolic side reflectors and parabolic lamellae. There are two versions: medium beam with an integrated white top reflector and narrow beam with an integrated mirror top reflector. Moreover, a prismatic acrylic cover (P) and a white steel louver (L-F) are available. The reflectors do not require the use of tools and are firmly fixed to the electrical units via a simple click-in and must be connected to each other in a light line with additional coupling pieces. End plates for the beginning and end of the light line are available as accessories.

### Product data

<b>General Information</b>			
Accessory color	White	Full product name	9MX056 EP-F WH
Product family code	9MX056 [ACC MAXOS]	Full product code	403073255284900
		Order code	910684015121
		Material Nr. (12NC)	910684015121
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	4030732552849
		Numerator - Packs per outer box	1
		EAN/UPC - Case	4030732552849
<b>Approval and Application</b>			
Ingress protection code	-		
Protection class IEC	-		
<b>Product Data</b>			
Order product name	9MX056 EP-F WH		