



Maxos TL-D, facet reflectors and optics

9MX056 CPF WH (2PCS)

ACC MAXOS, White

The design-orientated facettted reflectors for TL-D are ideal for applications focusing on trade (such as supermarkets and shops) and for offices. They are made of steel, with a white or silver finish, and are available for electrical units holding 1 or 2 TL-D lamps. The 2-lamp versions of the facettted reflectors must be used with special electrical units (lamp holder F32 mm). A facettted reflector comes without a pre-mounted mirror inlay and can be integrated with a semi-high-gloss (D6) OLC optic of high-quality aluminum. This optic has parabolic side reflectors and parabolic lamellae, and it can create either a medium beam (with an integrated white top reflector) or a narrow beam (with an integrated mirror top reflector). A prismatic acrylic screen to cover the facettted reflector is also available. For basic glare reduction, the facettted reflector can be equipped with a white-coated steel louver. The reflector is fixed on the electrical units via a simple click-in. The facettted reflectors must be connected to each other with additional coupling pieces. End plates for the beginning and end of the light line are available as accessories.

Product data

General Information		Product Data	
Accessory color	White	Order product name	9MX056 CPF WH (2PCS)
Product family code	9MX056 [ACC MAXOS]	Full product name	9MX056 CPF WH (2PCS)
Approval and Application		Full product code	403073255441600
Ingress protection code	-	Order code	910684016121
Protection class IEC	-	Material Nr. (12NC)	910684016121
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	4030732554416

Maxos TL-D, facet reflectors and optics

Numerator - Packs per outer box	1
EAN/UPC - Case	4030732554416

