



Maxos TL-D, trapeze reflectors and optics

4MX092 1 58 T WH

MAXOS R T8, 1, 58 W

The sturdy trapeze reflectors for TL-D are designed for standard applications in industry, supermarkets, and shops. They are made of steel with a white or silver coating. The reflectors are optimised for electrical units holding 1 or 2 TL-D lamps and provide an excellent light output ratio. There are basic trapeze reflectors without a mirror inlay and trapeze reflectors with different aluminium mirror inlays. These are suitable for wide beam, narrow beam, and asymmetrical wall washing light distributions. Moreover, perforated and slotted trapeze reflectors, without mirror inlays, can be ordered as design elements or to create an indirect uplighting effect. For glare reduction, the trapeze reflector can be equipped with a steel louver that has a white or silver coating. To use emergency lighting by separately connected orientation light units (E27-sockets), special trapeze reflectors with a cut-off must be selected. The length of this reflector corresponds with that of the 58 W trunking length. A 36 W-electrical unit plus the orientation light unit will fill this length. The reflectors are fixed on the electrical units via a simple click-in. The reflectors can also be connected to each other in a line without additional coupling pieces, as they are delivered with an integrated connection side at one end of the reflector. At the beginning and the end of the lightline end plates, as accessories, are available.

Product data

General Information		Light Technical	
Accessory color	White	Number of light sources	1
Product family code	4MX092 [MAXOS R T8]		

Maxos TL-D, trapeze reflectors and optics

Operating and Electrical

Power Consumption	58 W
-------------------	------

Mechanical and Housing

Overall length	1,530 mm
----------------	----------

Approval and Application



Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

Product Data

Order product name	4MX092 1 58 T WH
--------------------	------------------

Full product name	4MX092 1 58 T WH
Full product code	403073253898099
Order code	53898099
Material Nr. (12NC)	910690004026
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732538980
Numerator - Packs per outer box	6
EAN/UPC - Case	4030732108619

Dimensional drawing



Product

4MX092 1 58 T WH

