



Maxos TL-D, facet reflectors and optics

4MX092 1/2 36 F-S-D/I WH

MAXOS R T8, 36 W

The design-orientated faceted reflectors for TL-D are ideal for applications focusing on trade (such as supermarkets and shops) and for offices. They are made of steel, with a white or silver finish, and are available for electrical units holding 1 or 2 TL-D lamps. The 2-lamp versions of the faceted reflectors must be used with special electrical units (lamp holder F32 mm). A faceted reflector comes without a pre-mounted mirror inlay and can be integrated with a semi-high-gloss (D6) OLC optic of high-quality aluminum. This optic has parabolic side reflectors and parabolic lamellae, and it can create either a medium beam (with an integrated white top reflector) or a narrow beam (with an integrated mirror top reflector). A prismatic acrylic screen to cover the faceted reflector is also available. For basic glare reduction, the faceted reflector can be equipped with a white-coated steel louver. The reflector is fixed on the electrical units via a simple click-in. The faceted reflectors must be connected to each other with additional coupling pieces. End plates for the beginning and end of the light line are available as accessories.

Product data

General Information	
Accessory color	White
Product family code	4MX092 [MAXOS R T8]
Operating and Electrical	
Power Consumption	36 W

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Full product code	403073259963999
Order product name	4MX092 1/2 36 F-S-D/I WH
Order code	910690143026
Numerator - Quantity Per Pack	1

Maxos TL-D, facet reflectors and optics

Numerator - Packs per outer box	6
Material Nr. (12NC)	910690143026
Full product name	4MX092 1/2 36 F-S-D/I WH
EAN/UPC - Case	4030732202072

EAN/UPC - Product/Case	4030732599639
------------------------	---------------

