



# Maxos TL-D, facet reflectors and optics

4MX092 1/2 58 F-WB SI

MAXOS R T8, 58 W

The design-orientated faceted reflectors for TL-D are ideal for applications focussing on trade (such as supermarkets and shops) and for offices. They are made of steel, with a white or silver coating, and are available for electrical units holding 1 or 2 TL-D lamps. The 2-lamp versions of the faceted reflectors must be used with special electrical units (lampholder F32mm). There are faceted reflectors without a mirror inlay and faceted reflectors with different aluminium mirror inlays. These are suitable for wide beam and asymmetrical beam applications. Moreover, slotted faceted reflectors without mirror inlay can be ordered to create an indirect uplighting effect. When the faceted reflector comes without a pre-mounted mirror inlay it can be integrated with a semi-high-gloss (D6) OLC optic of high-quality aluminium. This optic has parabolic side reflectors and parabolic lamellae, and it can create either a medium beam (with an integrated white top reflector), or a narrow beam (with an integrated mirror top reflector). A prismatic screen to cover the faceted reflector is also available. For basic glare reduction, the faceted reflector can be equipped with a white-coated steel louver. The reflector is fixed on the electrical units via a simple click-in. The faceted reflectors must be connected to each other with additional coupling pieces. At the beginning and the end of the line, end plates, as accessories, are available.

## Product data


General Information		Operating and Electrical	
Accessory color	Silver	Power Consumption	58 W
Product family code	4MX092 [MAXOS R T8]		

Maxos TL-D, facet reflectors and optics

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	4MX092 1/2 58 F-WB SI
Full product name	4MX092 1/2 58 F-WB SI
Full product code	403073259971499
Order code	59971499

Material Nr. (12NC)	910690154126
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732599714
Numerator - Packs per outer box	6
EAN/UPC - Case	4030732202164

Dimensional drawing



Product
4MX092 1/2 58 F-WB SI

