



# Maxos TL-D, facet reflectors and optics

## 4MX092 1/2 58 F-WB SI

MAXOS R T8, 58 W

The design-orientated facettted reflectors for TL-D are ideal for applications focusing on trade (such as supermarkets and shops) and for offices. They are made of steel, with a white or silver finish, and are available for electrical units holding 1 or 2 TL-D lamps. The 2-lamp versions of the facettted reflectors must be used with special electrical units (lamp holder F32 mm). A facettted reflector comes without a pre-mounted mirror inlay and can be integrated with a semi-high-gloss (D6) OLC optic of high-quality aluminum. This optic has parabolic side reflectors and parabolic lamellae, and it can create either a medium beam (with an integrated white top reflector) or a narrow beam (with an integrated mirror top reflector). A prismatic acrylic screen to cover the facettted reflector is also available. For basic glare reduction, the facettted reflector can be equipped with a white-coated steel louver. The reflector is fixed on the electrical units via a simple click-in. The facettted reflectors must be connected to each other with additional coupling pieces. End plates for the beginning and end of the light line are available as accessories.

### Product data


General Information		Approval and Application	
Accessory color	Silver	Ingress protection code	IP20 [Finger-protected]
Product family code	4MX092 [MAXOS R T8]	Product Data	
Operating and Electrical		Full product code	403073259971499
Power Consumption	58 W	Order product name	4MX092 1/2 58 F-WB SI
		Order code	910690154126
		Numerator - Quantity Per Pack	1

# Maxos TL-D, facet reflectors and optics

Numerator - Packs per outer box	6
Material Nr. (12NC)	910690154126
Full product name	4MX092 1/2 58 F-WB SI
EAN/UPC - Case	4030732202164

EAN/UPC - Product/Case	4030732599714
------------------------	---------------

## Dimensional drawing



Product
4MX092 1/2 58 F-WB SI

