



Maxos TL5, facet reflectors and optics

4MX692 1/2 54 F SI

MAXOS R T5, 54 W

Facetted reflectors for TL5 give shops and offices a high-class appearance. They are made of steel, with a white or silver finish, and are available for electrical units holding 1 or 2 TL5 lamps. The facetted reflector can be integrated with a semi-high-gloss (D6) OLC optic of high-quality aluminum and has parabolic side reflectors and parabolic lamellae. There are two versions: medium beam with an integrated white top reflector and narrow beam with an integrated mirror top reflector. Moreover, a prismatic acrylic cover (P) and a white steel louver (L-F) are available. The reflectors do not require the use of tools and are firmly fixed to the electrical units via a simple click-in and must be connected to each other in a light line with additional coupling pieces. End plates for the beginning and end of the light line are available as accessories.


Product data

General Information		Approval and Application	
Accessory color	Silver	Ingress protection code	IP20 [Finger-protected]
Product family code	4MX692 [MAXOS R T5]	Product Data	
Operating and Electrical		Order product name	4MX692 1/2 54 F SI
Power Consumption	54 W	Full product name	4MX692 1/2 54 F SI
Mechanical and Housing		Full product code	403073258418599
Overall length	1,179 mm	Order code	58418599
		Material Nr. (12NC)	910691152026
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	4030732584185

Maxos TL5, facet reflectors and optics

Numerator - Packs per outer box	6
EAN/UPC - Case	4030732198931

Dimensional drawing



Product
4MX692 1/2 54 F SI

