



# Maxos TL5, facet reflectors and optics

4MX692 1/2 54 F SI

MAXOS R T5, 54 W

Facetted reflectors for TL5 give shops and offices a high-class appearance. They are made of steel, with a white or silver finish, and are available for electrical units holding 1 or 2 TL5 lamps. The facetted reflector can be integrated with a semi-high-gloss (D6) OLC optic of high-quality aluminum and has parabolic side reflectors and parabolic lamellae. There are two versions: medium beam with an integrated white top reflector and narrow beam with an integrated mirror top reflector. Moreover, a prismatic acrylic cover (P) and a white steel louver (L-F) are available. The reflectors do not require the use of tools and are firmly fixed to the electrical units via a simple click-in and must be connected to each other in a light line with additional coupling pieces. End plates for the beginning and end of the light line are available as accessories.

## Product data


General Information	
Accessory color	Silver
Product family code	4MX692 [MAXOS R T5]
Operating and Electrical	
Power Consumption	54 W
Mechanical and Housing	
Overall length	1,179 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	4MX692 1/2 54 F SI
Full product name	4MX692 1/2 54 F SI
Full product code	403073258418599
Order code	910691152026
Material Nr. (12NC)	910691152026
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732584185

# Maxos TL5, facet reflectors and optics

Numerator - Packs per outer box	6
EAN/UPC - Case	4030732198931

## Dimensional drawing



Product
4MX692 1/2 54 F SI

