



Maxos TL5, facet reflectors and optics

4MX692 1/2 49 F-S-D/I SI

MAXOS R T5, 49 W

Facetted reflectors for TL5 give shops and offices a high-class appearance. They are made of steel, with a white or silver finish, and are available for electrical units holding 1 or 2 TL5 lamps. The facetted reflector can be integrated with a semi-high-gloss (D6) OLC optic of high-quality aluminum and has parabolic side reflectors and parabolic lamellae. There are two versions: medium beam with an integrated white top reflector and narrow beam with an integrated mirror top reflector. Moreover, a prismatic acrylic cover (P) and a white steel louver (L-F) are available. The reflectors do not require the use of tools and are firmly fixed to the electrical units via a simple click-in and must be connected to each other in a light line with additional coupling pieces. End plates for the beginning and end of the light line are available as accessories.

Product data

General Information	
Accessory color	Silver
Product family code	4MX692 [MAXOS R T5]
Operating and Electrical	
Power Consumption	49 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	4MX692 1/2 49 F-S-D/I SI

Full product name	4MX692 1/2 49 F-S-D/I SI
Full product code	403073259984499
Order code	910691155026
Material Nr. (12NC)	910691155026
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732599844
Numerator - Packs per outer box	6
EAN/UPC - Case	4030732202249

Maxos TL5, facet reflectors and optics

