



# Maxos, TL-D IP63 reflector units

## 4MX093 1/2x58W L-F IP63 WH

MAXOS LLT8, 58 W

The reflector units IP54 are pre-assembled units combining the functions of regular electrical units and white reflectors with glass covers. They are made of steel, with white coating and are designed for reliable mounting into MAXOS IP64 trunking sections. For electrical connection to the trunking a connector block is mounted. MAXOS is not foreseen for regular humid environment. Wide beam and asymmetrical beam light distribution is possible. The reflector units IP54 are equipped with electronic ballasts and can hold one or two TL-D lamps 58W. Types with an integrated white louvre are available.

### Product data

General Information	
Accessory color	White
Product family code	4MX093 [MAXOS LLT8]
Operating and Electrical	
Power Consumption	58 W
Mechanical and Housing	
Housing Color	White
Approval and Application	
Ingress protection code	IP63 [Dust penetration-protected, rain/spray-proof]

Product Data	
Order product name	4MX093 1/2x58W L-F IP63 WH
Full product name	4MX093 1/2x58W L-F IP63 WH
Full product code	403073260694899
Order code	60694899
Material Nr. (12NC)	910695032026
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732606948
Numerator - Packs per outer box	6
EAN/UPC - Case	4030732209897