



Maxos, TL-D IP63 reflector units

4MX093 1/2x58W L-F IP63 WH

MAXOS LLT8, 58 W

Maxos IP63 closed reflector units are ready-to-install luminaires dedicated for Maxos light-line system and designed for industrial applications where good protection of reflectors against dust is requested in particular automotive industry or food industry. The unit can be easily cleaned with wet cloth if necessary. The housing is made of white coated steel; the cover from tempered glass or optional from polycarbonate (PC), inner aluminum reflector. Maxos IP63 closed reflector units are combining the functions of Maxos electrical units, reflectors and covers. Designed for reliable mounting against Maxos light-line sections in TL-D length. For electrical connection to the light line a connector block is mounted on top of the units. Mechanical connection is realized by a safe bracket with knee-lever clasp around the light line. IP63 classification is valid for complete lamp, optical and ballast compartment however total system including IP20 light-line sections is IP20. The standard range is 1-lamp and 2-lamp TL-D 58 W with HF or conventional ballast and TL5 80 W with HF ballast, all to be mounted against TL-D Maxos light-line system, optional with EL3 emergency lighting. The units come with inner aluminum reflectors for wide-beam (WB) or asymmetrical-beam (A) light distribution. White louvers (4MX093 1/2 58 L-IP63-unit WH) are available as accessories. Please note that Maxos is not designed for regular humid environment.

Product data

General Information		Operating and Electrical	
Accessory color	White	Power Consumption	58 W
Product family code	4MX093 [MAXOS LLT8]		

Maxos, TL-D IP63 reflector units

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Ingress protection code	IP63 [Dust penetration-protected, rain/spray-proof]
-------------------------	---

Product Data

Order product name	4MX093 1/2x58W L-F IP63 WH
--------------------	----------------------------

Full product name	4MX093 1/2x58W L-F IP63 WH
-------------------	----------------------------

Full product code	403073260694899
-------------------	-----------------

Order code	910695032026
------------	--------------

Material Nr. (12NC)	910695032026
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

EAN/UPC - Product/Case	4030732606948
------------------------	---------------

Numerator - Packs per outer box	6
---------------------------------	---

EAN/UPC - Case	4030732209897
----------------	---------------

