



Maxos TL-D, aluminum reflectors and optics

4MX092 1 58 D-A

MAXOS R T8, 1, 58 W

The aluminium reflectors for TL-D are optimised in light technical performance for applications in industry, supermarkets and shops. They are made of high-quality aluminium in one piece and are available for electrical units holding 1 or 2 TL-D lamps. The 2-lamp versions of the aluminium reflectors must be used with special electrical units (lampholder F32mm). For wide beam, narrow beam, and asymmetrical beam light distributions a semi-high-gloss (D) aluminium reflector is available. For very narrow beams, a high-gloss (C) aluminium reflector is available. Moreover, a perforated decorative high-gloss aluminium reflector in wide beam can be ordered. This perforated decorative reflector can be equipped with a decorative louvre with ring-lamellae in silver. The reflector is fixed on to the electrical unit via a simple click-in. The reflectors can be connected to each other in a line without additional coupling pieces or connection sides. There are no endplates available for the aluminium reflectors TL-D.

Product data

General Information	
Accessory color	Aluminum
Product family code	4MX092 [MAXOS R T8]
Light Technical	
Number of light sources	1


Operating and Electrical	
Power Consumption	58 W
Mechanical and Housing	
Overall length	1,530 mm

Maxos TL-D, aluminum reflectors and optics

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	4MX092 1 58 D-A
Full product name	4MX092 1 58 D-A
Full product code	403073254157799
Order code	54157799

Material Nr. (12NC)	910698004726
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732541577
Numerator - Packs per outer box	12
EAN/UPC - Case	4030732111053

Dimensional drawing



Product
4MX092 1 58 D-A

