



Maxos TL5, aluminum reflectors and optics

4MX692 1/2 54 D-MB

MAXOS R T5, 54 W

The aluminum reflectors for TL5 are optimised for applications in supermarkets, shops and industry. They are made of high-quality aluminum and are available for electrical units holding 1 or 2 TL5 lamps. A semi-high-gloss (D) aluminum reflector is available for wide-beam, medium-beam, narrow-beam, asymmetrical-beam and double-asymmetrical-beam light distributions. For very narrow beams a high-gloss (C) aluminum reflector is available. All the TL5 aluminum reflectors can be equipped with aluminum louvers with profiled lamellae (M2) or with a simple white steel louver (L) for glare reduction. The reflector is fixed to the electrical unit via a simple click. The reflectors can be connected to each other in a line by a material overlap; optional additional coupling pieces (9MX056 CP/TL5) are available. Decorative end plates for the beginning and end of the line are available as accessories.


Product data

General Information		Approval and Application	
Accessory color	Aluminum	Ingress protection code	IP20 [Finger-protected]
Product family code	4MX692 [MAXOS R T5]		
Operating and Electrical		Product Data	
Power Consumption	54 W	Order product name	4MX692 1/2 54 D-MB
		Full product name	4MX692 1/2 54 D-MB
		Full product code	403073258424699
		Order code	910699102526
		Material Nr. (12NC)	910699102526
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	4030732584246
Mechanical and Housing			
Overall length	1,179 mm		

Maxos TL5, aluminum reflectors and optics

Numerator - Packs per outer box	12
EAN/UPC - Case	4030732199068

Dimensional drawing



Product
4MX692 1/2 54 D-MB

