



# Maxos TL5, aluminum reflectors and optics

## 4MX692 1/2 49 C-NB

MAXOS R T5, 49 W

The aluminum reflectors for TL5 are optimised for applications in supermarkets, shops and industry. They are made of high-quality aluminum and are available for electrical units holding 1 or 2 TL5 lamps. A semi-high-gloss (D) aluminum reflector is available for wide-beam, medium-beam, narrow-beam, asymmetrical-beam and double-asymmetrical-beam light distributions. For very narrow beams a high-gloss (C) aluminum reflector is available. All the TL5 aluminum reflectors can be equipped with aluminum louvers with profiled lamellae (M2) or with a simple white steel louver (L) for glare reduction. The reflector is fixed to the electrical unit via a simple click. The reflectors can be connected to each other in a line by a material overlap; optional additional coupling pieces (9MX056 CP/TL5) are available. Decorative end plates for the beginning and end of the line are available as accessories.


### Product data

<b>General Information</b>		<b>Approval and Application</b>	
Accessory color	Aluminum	Ingress protection code	IP20 [Finger-protected]
Product family code	4MX692 [MAXOS R T5]	<b>Product Data</b>	
<b>Operating and Electrical</b>		Order product name	4MX692 1/2 49 C-NB
Power Consumption	49 W	Full product name	4MX692 1/2 49 C-NB
<b>Mechanical and Housing</b>		Full product code	403073258431499
Overall length	1,479 mm	Order code	58431499
		Material Nr. (12NC)	910699103926
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	4030732584314

Maxos TL5, aluminum reflectors and optics

Numerator - Packs per outer box	12
EAN/UPC - Case	4030732199136

Dimensional drawing



Product
4MX692 1/2 49 C-NB

