



Maxos TL5, universal reflectors and optics

4MX692 1/2x49W R IP60 WH

MAXOS R T5, 49 W


Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Full product name	
Accessory color	White	Full product code	403073224756100
Product family code	4MX692 [MAXOS R T5]	Order code	910699110226
Operating and Electrical		Material Nr. (12NC)	910699110226
Power Consumption	49 W	Numerator - Quantity Per Pack	1
Approval and Application		EAN/UPC - Product/Case	4030732247561
Ingress protection code	IP60 [Dust penetration-protected]	Numerator - Packs per outer box	1
Product Data		EAN/UPC - Case	4030732247561
Order product name	4MX692 1/2x49W R IP60 WH		

Maxos TL5, universal reflectors and optics

Dimensional drawing



Product
4MX692 1/2x49W R IP60 WH

