



# Maxos TL-D, universal reflectors and optics

## 4MX092 1/2x58W R IP60 SI

MAXOS R T8, 58 W


Maxos TL-D Universal reflectors are designed for electrical units holding 1 x TL-D lamp or, upon request, 2 x TL-D. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL-D Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

### Product data

<b>General Information</b>		<b>Full product name</b>	
Accessory color	Silver	4MX092 1/2x58W R IP60 SI	
Product family code	4MX092 [MAXOS R T8]	<b>Full product code</b>	
		403073224759200	
		<b>Order code</b>	
		910699110526	
		<b>Material Nr. (12NC)</b>	
		910699110526	
<b>Operating and Electrical</b>		<b>Numerator - Quantity Per Pack</b>	
Power Consumption	58 W	1	
		<b>EAN/UPC - Product/Case</b>	
		4030732247592	
		<b>Numerator - Packs per outer box</b>	
		1	
		<b>EAN/UPC - Case</b>	
		4030732247592	
<b>Approval and Application</b>			
Ingress protection code	IP60 [Dust penetration-protected]		
<b>Product Data</b>			
Order product name	4MX092 1/2x58W R IP60 SI		

Maxos TL-D, universal reflectors and optics

Dimensional drawing



Product

4MX092 1/2x58W R IP60 SI

