



Maxos TL5, universal reflectors and optics

4MX692 1/2x49W R IP60 SI

MAXOS R T5, 49 W


Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Full product name		4MX692 1/2x49W R IP60 SI
Accessory color	Silver	Full product code		403073224760800
Product family code	4MX692 [MAXOS R T5]	Order code		910699110626
		Material Nr. (12NC)		910699110626
Operating and Electrical		Numerator - Quantity Per Pack		1
Power Consumption	49 W	EAN/UPC - Product/Case		4030732247608
		Numerator - Packs per outer box		1
Approval and Application		EAN/UPC - Case		4030732247608
Ingress protection code	IP60 [Dust penetration-protected]			
Product Data				
Order product name	4MX692 1/2x49W R IP60 SI			

Maxos TL5, universal reflectors and optics

Dimensional drawing



Product
4MX692 1/2x49W R IP60 SI

