



Maxos TL-D, universal reflectors and optics

4MX093 1/2x58W AC IP60

MAXOS LLT8, 58 W

Maxos TL-D Universal reflectors are designed for electrical units holding 1 x TL-D lamp or, upon request, 2 x TL-D. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL-D Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Full product name	
Accessory color	-	Full product code	4MX093 1/2x58W AC IP60
Product family code	4MX093 [MAXOS LLT8]	Order code	403073265278599
Operating and Electrical		Material Nr. (12NC)	65278599
Power Consumption	58 W	Numerator - Quantity Per Pack	910699110926
Approval and Application		EAN/UPC - Product/Case	1
Ingress protection code	IP60 [Dust penetration-protected]	Numerator - Packs per outer box	4030732652785
Product Data		EAN/UPC - Case	6
Order product name	4MX093 1/2x58W AC IP60		