



# Maxos TL5, universal reflectors and optics

4MX693 1/2x54W AC IP60

MAXOS LLT5, 54 W

Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

## Product data

<b>General Information</b>		<b>Order product name</b>	
Accessory color	-	Order code	4MX693 1/2x54W AC IP60
Product family code	4MX693 [MAXOS LLT5]	Numerator - Quantity Per Pack	910699111026
<b>Operating and Electrical</b>		Numerator - Packs per outer box	1
Power Consumption	54 W	Material Nr. (12NC)	6
<b>Approval and Application</b>		Full product name	910699111026
Ingress protection code	IP60 [Dust penetration-protected]	EAN/UPC - Case	4MX693 1/2x54W AC IP60
<b>Product Data</b>		EAN/UPC - Product/Case	4030732247646
Full product code	403073265279299		4030732652792