



# Maxos TL5, universal reflectors and optics

## 4MX693 1/2x49W AC IP60

MAXOS LLT5, 49 W

Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

### Product data

General Information		Order product name	
Accessory color	-	Order code	4MX693 1/2x49W AC IP60
Product family code	4MX693 [MAXOS LLT5]	Numerator - Quantity Per Pack	910699111126
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	6
		Full product name	910699111126
		EAN/UPC - Case	4MX693 1/2x49W AC IP60
		EAN/UPC - Product/Case	4030732247653
			4030732652808
Operating and Electrical			
Power Consumption	49 W		
Approval and Application			
Ingress protection code	IP60 [Dust penetration-protected]		
Product Data			
Full product code	403073265280899		