



Maxos TL5, universal reflectors and optics

4MX693 1/2x54W PC IP60

MAXOS LLT5, 54 W

Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Full product name	4MX693 1/2x54W PC IP60
Accessory color	-	Full product code	403073265283999
Product family code	4MX693 [MAXOS LLT5]	Order code	65283999
Operating and Electrical		Material Nr. (12NC)	910699111426
Power Consumption	54 W	Numerator - Quantity Per Pack	1
Approval and Application		EAN/UPC - Product/Case	4030732652839
Ingress protection code	IP60 [Dust penetration-protected]	Numerator - Packs per outer box	6
Product Data		EAN/UPC - Case	4030732247684
Order product name	4MX693 1/2x54W PC IP60		