



Maxos TL-D, universal reflectors and optics

4MX092 1/2x36W R WH

MAXOS R T8, 36 W


Maxos TL-D Universal reflectors are designed for electrical units holding 1 x TL-D lamp or, upon request, 2 x TL-D. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL-D Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Order product name	
Accessory color	White	Order code	4MX092 1/2x36W R WH
Product family code	4MX092 [MAXOS R T8]	Numerator - Quantity Per Pack	910699111626
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	6
		Full product name	910699111626
		EAN/UPC - Case	4MX092 1/2x36W R WH
		EAN/UPC - Product/Case	4030732247707
			4030732652853
Operating and Electrical			
Power Consumption	36 W		
Approval and Application			
Ingress protection code	IP20 [Finger-protected]		
Product Data			
Full product code	403073265285399		

Maxos TL-D, universal reflectors and optics

Dimensional drawing



Product

4MX092 1/2x36W R WH

