



# Maxos TL5, universal reflectors and optics

## 4MX692 1/2x49W R SI

MAXOS R T5, 49 W


Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

### Product data

<b>General Information</b>		<b>Full product name</b>	
Accessory color	Silver	Full product code	403073265291499
Product family code	4MX692 [MAXOS R T5]	Order code	65291499
<b>Operating and Electrical</b>		Material Nr. (12NC)	910699112226
Power Consumption	49 W	Numerator - Quantity Per Pack	1
<b>Approval and Application</b>		EAN/UPC - Product/Case	4030732652914
Ingress protection code	IP20 [Finger-protected]	Numerator - Packs per outer box	6
<b>Product Data</b>		EAN/UPC - Case	4030732247769
Order product name	4MX692 1/2x49W R SI		

## Maxos TL5, universal reflectors and optics

### Dimensional drawing



#### Product

4MX692 1/2x49W R SI

