



# Maxos TL-D, universal reflectors and optics

## 4MX093 1x58W MB-R

MAXOS LLT8, 1, 58 W

Maxos TL-D Universal reflectors are designed for electrical units holding 1 x TL-D lamp or, upon request, 2 x TL-D. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL-D Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

### Product data

General Information		Product Data	
Accessory color	-	Order product name	4MX093 1x58W MB-R
Product family code	4MX093 [MAXOS LLT8]	Full product name	4MX093 1x58W MB-R
Light Technical		Full product code	403073265302799
Number of light sources	1	Order code	910699113326
Operating and Electrical		Material Nr. (12NC)	910699113326
Power Consumption	58 W	Numerator - Quantity Per Pack	1
Approval and Application		EAN/UPC - Product/Case	4030732653027
Ingress protection code	-	Numerator - Packs per outer box	6
		EAN/UPC - Case	4030732247875