



Maxos TL5, universal reflectors and optics

4MX693 1/2x49W A-R

MAXOS LLT5, 49 W

Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Full product name	
Accessory color	-	Full product code	4MX693 1/2x49W A-R
Product family code	4MX693 [MAXOS LLT5]	Order code	403073265316499
Operating and Electrical		Material Nr. (12NC)	65316499
Power Consumption	49 W	Numerator - Quantity Per Pack	910699114726
Approval and Application		EAN/UPC - Product/Case	1
Ingress protection code	-	Numerator - Packs per outer box	4030732653164
Product Data		EAN/UPC - Case	6
Order product name	4MX693 1/2x49W A-R		