



Maxos TL-D, universal reflectors and optics

4MX093 1/2x36W L-R WH

MAXOS LLT8, 36 W

Maxos TL-D Universal reflectors are designed for electrical units holding 1 x TL-D lamp or, upon request, 2 x TL-D. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL-D Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information	
Accessory color	White
Product family code	4MX093 [MAXOS LLT8]
Operating and Electrical	
Power Consumption	36 W
Approval and Application	
Ingress protection code	-
Product Data	
Order product name	4MX093 1/2x36W L-R WH

Full product name	4MX093 1/2x36W L-R WH
Full product code	403073265317199
Order code	65317199
Material Nr. (12NC)	910699114826
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732653171
Numerator - Packs per outer box	6
EAN/UPC - Case	4030732248025