



Maxos TL5, universal reflectors and optics

4MX693 1/2x49W

MAXOS LLT5, 49 W

Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Full product name	
Accessory color	White	Full product code	403073265320199
Product family code	4MX693 [MAXOS LLT5]	Order code	65320199
Operating and Electrical		Material Nr. (12NC)	910699115126
Power Consumption	49 W	Numerator - Quantity Per Pack	1
Approval and Application		EAN/UPC - Product/Case	4030732653201
Ingress protection code	-	Numerator - Packs per outer box	6
Product Data		EAN/UPC - Case	4030732248056
Order product name	4MX693 1/2x49W		