



Maxos TL5, universal reflectors and optics

4MX693 1/2x49W

MAXOS LLT5, 49 W

Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Order product name	
Accessory color	White	Order code	4MX693 1/2x49W
Product family code	4MX693 [MAXOS LLT5]	Numerator - Quantity Per Pack	910699115126
Operating and Electrical		Numerator - Packs per outer box	1
Power Consumption	49 W	Material Nr. (12NC)	6
Approval and Application		Full product name	910699115126
Ingress protection code	-	EAN/UPC - Case	4MX693 1/2x49W
Product Data		EAN/UPC - Product/Case	4030732248056
Full product code	403073265320199		