



Maxos TL5, universal reflectors and optics

4MX693 1/2x49W AC-MLO-R

MAXOS LLT5, 49 W

Maxos TL5 Universal reflectors are designed for electrical units holding 1 x or 2 x TL5 lamps. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL5 Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information	
Accessory color	-
Product family code	4MX693 [MAXOS LLT5]
Operating and Electrical	
Power Consumption	49 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Full product code	403073265324999

Order product name	4MX693 1/2x49W AC-MLO-R
Order code	910699115926
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	910699115926
Full product name	4MX693 1/2x49W AC-MLO-R
EAN/UPC - Case	4030732248131
EAN/UPC - Product/Case	4030732653249