



Maxos TL-D, universal reflectors and optics

9MX056 EP-R SI (2PCS)

ACC MAXOS, Silver

Maxos TL-D Universal reflectors are designed for electrical units holding 1 x TL-D lamp or, upon request, 2 x TL-D. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL-D Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

General Information		Full product name	
Accessory color	Silver	Full product code	403073224819300
Product family code	9MX056 [ACC MAXOS]	Order code	910699116526
Approval and Application		Material Nr. (12NC)	910699116526
Ingress protection code	-	Numerator - Quantity Per Pack	1
Protection class IEC	-	EAN/UPC - Product/Case	4030732248193
Product Data		Numerator - Packs per outer box	1
Order product name	9MX056 EP-R SI (2PCS)	EAN/UPC - Case	4030732248193